

# Mini - Focus X-ray Generator TRIX - 150M

# 150kV-100 μ m Mini-Focus X-ray Generator



### [Main Features]

- High output of 150kV-75W enables the inspection of Power devices and Castings which have poor radiolucency.
  Clear and sharp image can be obtained with its 100 μ m
  Mini-focus.
- Low noise X-ray Generator of high frequency inverter-control having high output and excellent stability.
- Remote setting of kV and mA is possible.
- Continuous run is possible.

#### [Applications]

- Inspection of Power devices
- Inspection of Castings


# [Specifications]

	TRIX-150M
Output: Tube Voltage	30.0∼150.0kV
Tube Current	0.2~0.5mA
Focus Size	$100~\mu$ m
Beam Angle	Perpendicular to tube axis:35°, Tube axis:A side $7.5^{\circ}$ 、C side $17.5^{\circ}$
Inhereht Filtration	1.00mm Be
High-tension Circuit	Inverter circuit with neutral grounding
Insulation	Oil insulation
Cooling	Forced air cooling (Blower cooling)
Continuous Run	Continuous run possible up to oil temp. 60°C in Generator (Continuous run possible with ambient temp. under 25°C)
Safety Circuit	1. Emergency stop button switch
	2. Protection circuits (Automatically function and display on operator panel.)
	Protection circuit for tube over-voltage and over-current, Protection circuit for primary over-voltage and over-current, Trouble in filament control circuit, Trouble in voltage power, Thermo-switch
Connectors	1. Interlock door switch input connector
	2. X-ray ON signal output connector (relay contact)
	3. Remote control connector
	Built-in/Remote switch, X-ray ON/OFF, kV-mA set (DC-V input)
Radiation Leakage (outside of beam cone)	less than 2.6mGy/h
Input Power	AC90 $\sim$ 110V or 180 $\sim$ 220V selectable, 50/60Hz
Usage Environment	Ambient Temp: $+5^{\circ}$ C $+35^{\circ}$ C, Relative Humidity: less than 85%(no dew)
Storage Temp.	0°C∼50°C
Weight: Generator Controller	ca. 45kg ca. 15kg
Accessories (Standard)	Power Cable (10m), Ground Cable (10m), Low-tension Cable (10m)
	Interlock Cable (10m), X-ray ON Output Cable(10m), Remote Control Cable (5m)
	Fuse(2pcs), Power-source Key(1pc), Operation Manual





# [Outside Dimension]


## X-ray Generator



### X-ray Controller







Office: Jl. Radin Inten II No. 62 Duren Sawit, Jakarta 13440 - Indonesia

Mobile: +62 816 1740 8925 Fax: 021-8690 6771

Workshop: Jl. Pahlawan Revolusi No. 22B, Jakarta 13430 - Indonesia Phone: 021-8690 6777 (Hunting)